


# NOVA Mouse Pads


Technical data sheet

## The CPS NOVA - Concept Precision System

“ *More than just a mousepad,  
a drive surface of great precision.* ”



A design specially developed for  
a strong visual impact.




### MAJOR ASSETS

- Precision
- Technicity
- Ergonomics
- Brilliance of colours

### THE PACKAGING

Allows the product to  
be seen and touched.



- Mono-material conception, non-glued, therefore cannot detach.
- 440 domes per cm<sup>2</sup> for precise movement without dirtying the mouse.
- The CPS quality is guaranteed by NOVA.
- Delivered exclusively in individual packaging.
- Customized quadri-chrome offset.
- Standard format : useful printed diameter : 195 mm, thickness : 1,5 mm.

# Technical documents to be supplied

## NOVA CPS

### In quadri-chrome offset

Printing technique using four primary colours : black, magenta, cyan and yellow ; spread and distributed in points, which permits the obtention of all nuances (photo quality).

### We can prepare your films. The minimum that must be supplied is :

- The implantation that you would like for your texts and graphics in a Ø 185 mm format.
- The logos : as big and precise as possible
- Originals of your drawings or paintings, the etchings or photos that you want to be reproduced.

### If you supply a computerised support :

Prepare your visual in a Ø 185 mm format and specify the colour and orientation of the frame.

We will integrate your image inside it.

[Ask for our specification sheet.](#)

### If you supply your films :


**Warning : if you send them by post, insure that they are packed in rigid cardboard.**

**WE SUPPLY YOU WITH THE FRAME** (Adobe Illustrator 7.0 file) by e-mail, digital network or on disk.

You just have to integrate your image into the interior of the circle and choose the background colour of the frame and its orientation.

The limits of the pad must not show on the films.

A film is not just a simple transparency, it must be inactinic.



- Sensitive layer on reading sense side (printing is done on verso-side of transparency).
- Trame 133 (definition)
- Supply a roller copy (Cromalin).
- Realize grey scale tones in black frame and not by colour separation.
- For black tones : colour with 40% blue and not with the 4 basic colours.
- For black texts and graphics : put in bold.



**Caution !** because the NOVA mouse mats are printed on a coarse clear plastic surface, colour sharpness and brightness may vary slightly from original proof.

**[Please don't hesitate to ask our advice!](#)**


# NOVA mousepad

CPS NOVA

## The Concept Precision System




### *Existing Formats*



- Standard format:  $\varnothing$  195 mm + slight point  
Sandy surface :  $\varnothing$  185 mm



- Other format : Rectangular 230x195 mm,  
Sandy surface : 210x185 mm



- Other format : square 200x200 mm,  
Sandy surface : 190x190 mm

# Real size of standard format CPS

CPS NOVA

